




RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20[.008] THICK STENCIL

4	35.56 [1.400]	14	37.69 [1.484]	30	3-1977937-0
4	2.54 [.100]	1	4.67 [.184]	4	1977937-4
PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOJAL 17AUG2013	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK MIKE MILLER 17AUG2013	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		AP'D MIKE MILLER 17AUG2013	SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY,VERTICAL, DOUBLE ROW, .100 X .100 C/L, .025 SQ.POST,30 Pd/Ni	
		PRODUCT SPEC	APPLICATION SPEC	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT	SIZE	CAGE CODE DRAWING NO
MATERIAL		—	A1	00779 C=1977937
FINISH		—	RESTRICTED TO	
SEE TABLE		CUSTOMER DRAWING		
		SCALE 8:1 SHEET 1 OF 1 REV C		