






**CONNECTOR
 DESIGNATORS
 A-F-H-L-S
 SELF-LOCKING
 ROTATABLE
 COUPLING**




STYLE 2
 (STRAIGHT
 See Note 1)



STYLE F
 Light Duty
 (Table V)



STYLE G
 Light Duty
 (Table IV)



STYLE L
 Light Duty
 (Table V)

400-015
TAG® Ring Backshell
 with Strain Relief
 Self-Locking Rotatable Coupling - Straight Only



See inside back cover
 fold-out or pages 13 and
 14 for Tables I and II.

TABLE IV: CABLE ENTRY					
Dash No.	K Max		Cable Entry Max		
02	.545	(13.8)	.250	(6.4)	
03	.670	(17.0)	.375	(9.5)	
04	.795	(20.2)	.500	(12.7)	
05	.920	(23.4)	.625	(15.9)	
06	1.045	(26.5)	.750	(19.1)	
07	1.170	(29.7)	.875	(22.2)	
08	1.295	(32.9)	1.000	(25.4)	
09	1.420	(36.1)	1.125	(28.6)	
10	1.670	(42.4)	1.250	(31.8)	

TABLE V: CABLE ENTRY						
Dash No.	L Max	Cable Range				
		Min		Max		
02	.968 (24.6)	.125	(3.2)	.250	(6.4)	
03	1.046 (26.6)	.250	(6.4)	.375	(9.5)	
04	1.156 (29.4)	.250	(6.4)	.500	(12.7)	
05	1.218 (30.9)	.375	(9.5)	.625	(15.9)	
06	1.343 (34.1)	.500	(12.7)	.750	(19.1)	
07	1.468 (37.3)	.625	(15.9)	.875	(22.2)	
08	1.593 (40.5)	.625	(15.9)	1.000	(25.4)	
09	1.718 (43.6)	.750	(19.1)	1.125	(28.6)	
10	1.843 (46.8)	.875	(22.2)	1.250	(31.8)	

1. When maximum cable entry (page 21) is exceeded, Style 2 will be supplied. Please consult factory.
2. Metric dimensions (mm) are indicated in parentheses.
3. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Consult factory for shorter lengths on straight backshells.