




LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
BD	35				0	RLSE, WAS 91-5029-1, NPR 3371	4-91	KB
				A	REV PER ECN BD5278	08/13/91	KB	
				B	REV PER ECN BD5637	05/29/92	KB	
				C	REV PER EC 0020-155-94	03/10/94	AF	
				D	REV PER EC 0020-0740-94	07/13/94	AF	
				E	REV PER EC 0020-0657-95	06/27/95	RB	




1 1/8-18 UNEF-2A
PD 27.622 MAX
[1.0875]
MAJOR DIA 28.539 MAX
[1.1236]

4.06 MAX
[.160] PANEL THICKNESS
7.62 [.300] 4 PLC

3.05±0.08 DIA
[.120±.003] 4 PLC

CAVITY IDENTIFICATION LETTERS
BOTH SIDES



- 1. AMP PART NO APPEARS ON THIS SURFACE.
- 2. THIS PART ACCEPTS TYPE III+ SOCKET CONTACTS.
- 3. RECEPTACLE MATES WITH PRODUCT DESIGNED TO MIL SPEC 5015.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13[.005] 3 PLC DEC ± - ANGLES ± 1°				213667-1			
MATERIAL POLYAMID, BLACK				PART NO			
FINISH -				AMP Incorporated Harrisburg, PA 17105-3608			
DR 4-29-91 J McCLINTON				NAME			
CHK 5-2-91 R.STONE				RECEPTACLE HOUSING, 18-10, REVERSE SEX, SQUARE FLANGE, CPC			
APPD 5-2-91 K.BEAVER				SIZE			
APPD 5-2-91 J.FULPONI				CAGE CODE			
PRODUCT SPEC 108-10024				DRAWING NO			
APPLICATION SPEC 114-10004				213667			
WEIGHT -				SHEET 1 OF 1			