





1 2 3 4 5 6 7 8



BOARD TO BOARD CONTACT POST
FOR 0.8 MIN. DIA HOLE



ENLARGE VIEW
DETAIL P



SEE VIEW
DETAIL P

NOTES:

- PRODUCT SPECIFICATION : 108-19041
- PACKAGING: ON PLASTIC TUBES, BOXED

CONTACT: 0,4µm MIN SELECTIVE GOLD PLTD ON MATING CONTACT AREA AND 3,0µm MIN TIN PLTD ON CONTACT POST, OVER 1,25µm MIN NI PLTD UNDERLAYER			HOUSING: THERMOPLASTIC POLYESTER 20% GF, UL94-v0 COLOUR GREEN CONT. : PH. BRONZE H06			215391-6				
			FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)			
			CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLD PER RIFERIMENTO				
			THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION 19				
			© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING							
			TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES: UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE) —		RANGO FILO (WIRE RANGE) —			
			± 0,3		tyco		AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)			
			± 2°							
00-0047-04 D. C. 2004			ANGOLI (ANGLES)		Electronics		6 POS. 2.54 CENTRE AMP-EDGE CONN. ASS'Y DUAL LOADED WITH B.T.B. CONT. 90° VERSION			
00-0147-03 D. C. 21 AUG 2003			DIS. 15 NOV 01 (DR.) G. SINCHETTO							
00-0115-03 D. C. 04 JUL 2003			CONT. 15 NOV 01 (CHK) C. TARTARI		LOC.		SIZE	NUMERO (DWG NO)	REV.	FOGLIO (SHEET)
00-0068-03 PB 08 NOV 03					I		A3	C-215391	J3	1 (OF) 1
D ET00-0275 01 GS CT NOV 01			APP. (APP.)							
NI RECORD			DATA (DATE)							