

NOTES:

1. SPECIFICATIONS

Current Rating: 1A AC,DC

Voltage Rating: 125V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max.

Insulation Resistance: 100MΩ Min.

Withstanding Voltage: 500V AC/minute

Material: Natural Thermoplastic, UL94V-0

2. Part number of terminal for wire assembly: 10114827

3. Ordering Information & Dimensions:

10114826- X 0 X XX LF

LF: See note A

Material



0: PA66 Natural

1: PA66 Black


pin counts from 02~15

Packaging

0: Bulk



ONLY 2 CIRCUITS



ONLY 3 CIRCUITS

PART NO.	Dimensions				
	A	B	C	D	E
10114826-x0x02LF	4.25	1.25±0.05	2.95		3.47
10114826-x0x03LF	5.50	2.50±0.10	4.20		4.72
10114826-x0x04LF	6.75	3.75±0.10	5.45	2.50±0.10	5.97
10114826-x0x05LF	8.00	5.00±0.10	6.70	3.75±0.10	7.22
10114826-x0x06LF	9.25	6.25±0.15	7.95	5.00±0.15	8.47
10114826-x0x07LF	10.50	7.50±0.15	9.20	6.25±0.15	9.72
10114826-x0x08LF	11.75	8.75±0.15	10.45	7.50±0.15	10.97
10114826-x0x09LF	13.00	10.00±0.15	11.70	8.75±0.15	12.22
10114826-x0x10LF	14.25	11.25±0.20	12.95	10.00±0.20	13.47
10114826-x0x11LF	15.50	12.50±0.20	14.20	11.25±0.20	14.72
10114826-x0x12LF	16.75	13.75±0.20	15.45	12.50±0.20	15.97
10114826-x0x13LF	18.00	15.00±0.20	16.70	13.75±0.20	17.22
10114826-x0x14LF	19.25	16.25±0.20	17.95	15.00±0.20	18.47
10114826-x0x15LF	20.50	17.50±0.20	19.20	16.25±0.20	19.72

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406	ISO 101	WTB		
ltr				ecn no	dr	date	title		
A				T10-0145	JH	12/1/10	WTB 1.25MM HOUSING		
B				ELX-N-23435	TIM	03/02/16			
							dwg no		
							sheet 1 of 1		
							10114826		
							A3		
							type		
							Product Customer Drawing		
sheet				revision	B				
index				sheet	1				