





SUGGESTED PANEL CUTOUT



PANEL THICKNESS	X
0.030~0.049 [0.75~1.25]	0.756 [19.2]
0.049~0.079 [1.25~2.00]	0.764 [19.4]
0.079~0.118 [2.00~3.00]	0.772 [19.6]

SCHEMATIC



SPECIFICATIONS

FUNCTION:
1P1T OFF-ON

RATINGS:
ANSI/UL 1054 AND CAN/CSA C22.2 NO. 55 (E194579):
10A 125VAC [UR, cUR]

CONTACT RESISTANCE:
INITIAL: 35mΩ Max. AT 50VAC

INSULATION RESISTANCE:
100MΩ MIN. AT 500VDC

DIELECTRIC STRENGTH:
1,500VAC FOR 1 Minute

ELECTRICAL LIFE:
6,000 CYCLES [UR, cUR]

TEMPERATURE:
OPERATING: -20°C TO 105°C [UR, cUR]

APPROVALS:



COLORS AND MARKINGS

BODY:
BLACK

ACTUATOR:
WHITE

MARKINGS:
NO MARKINGS

MARKING COLOR:
NONE

Object ID: 100088870

ACTUATOR	A	09/30/16	MJR
BODY	A	09/30/16	MJR
COLORS	A	09/30/16	MJR
MATERIALS	A	09/30/16	MJR
SPECIFICATIONS	A	09/30/16	MJR
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH-LAMB INDUSTRIES AND IS NOT TO BE COPIED OR TRANSFERRED

A	INITIAL RELEASE	22532	09/30/16	MJR
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE

 E ♦ SWITCH®		 LAMB INDUSTRIES	
TITLE			
RD11131200			
ITEM NUMBER		DATE	REVISION
38-RD11131200		SEPTEMBER 30, 2016	A