




REVISIONS			
SYM	ZONE	ECN, ERN NO.	DATE
A		PROPOSAL	06/02/27
B		PER ECN E07135	JUN 5/07
C		UPDATE PER ACTUAL PART.	OCT22/15



FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0
COLOR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: MATING AREA: SELECTIVELY PLATED GOLD—PER
PART NUMBER OPTIONS
50 MICROINCH [1.27 MICRONS] MIN. NICKEL OVERALL
100 MICROINCH [2.54 MICRONS] MIN. MATTE TIN
OR GOLD FLASH OVER TAIL

AMPHENOL PART NUMBER: RJE07-188-0X10

GOLD PLATING
1 = 06 MICROINCH
2 = 15 MICROINCH
3 = 30 MICROINCH
4 = 50 MICROINCH



DRAWN PAULW	DATE 06/02/27	Amphenol Canada Corp.	
DESIGNED			
CHECKED CHIGOW	06/02/27	TITLE RJE07 SURFACE MOUNT MODULAR JACK 8 POSITION, 8 CONTACTS, WITHOUT SHIELD, WITHOUT FLANGE AND WITHOUT KEY – RoHS COMPLIANT	
I. E. APPRD. JEFF.S	JUN 5/07		
Q. A. APPRD. KENT.Y	JUN 5/07	DWG DRAWING NO. P-RJE07-188-0X10	
DWG. APPRD.			
ENG. REL. NO. E07135		REF. C	
DIMENSIONS ARE IN inches (mm)	CODE ID. NO. 03554		
SCALE	WT. -----	SURF. -----	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.