



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE ----- 30 LB MAX		2X S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ----- 4 LB MIN		LOAD	28 VDC		ONE PLACE (.0) ±.030
PRETRAVEL ----- .040 MAX			SEA LEVEL	50,000 FT.	TWO PLACE (.00) ±.015
DIFFERENTIAL TRAVEL ----- .020 MAX		RES	4	4	THREE PLACE (.000) ±.005
OVERTRAVEL ----- .250 MIN		IND	2	2	ANGLES ±
		MOTOR	4		WEIGHT 20.50 OZ MAX
		LAMP			

ANSI Y14.5M-1982 APPLIES