





---	.120	8333648P1	1-206503-2	1-206503-2
---	.120	570566-4	1-206503-1	1-206503-1
	.120	311P407-4S-B-12	206503-4	206503-9
	.120	20025720P1062S	206503-8	206503-8
---	.154	SC81D139-044	206503-7	206503-7
	.120	R4383P62S	206503-6	206503-6
	.120	R4383P62S-2	206503-5	206503-5
	.120	311P407-4S-B-12	206503-4	206503-4
---	.154	N/A	206503-3	206503-3
---	.120	R9259P62S	206503-2	206503-2
	.154	311P407-4S-B-15	206503-1	206503-1
REMARKS	DIA A	CUSTOMER P/N ON CONNECTOR	TE P/N ON CONNECTOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						OWN A.J.GRAFF		12-21-92				TE Connectivity	
DIMENSIONS: INCHES 						CNC D.MILLER		12-21-92		NAME AMPLIMITE RCPT ASSY,NON-MAGNETIC, SHELL SIZE 4.62 POSITION			
						APPROV D.MILLER		12-21-92					
						PRODUCT SPEC							
						APPLICATION SPEC							
MATERIAL						SIZE		GAGE CODE		DRAWING NO		RESTRICTED TO	
SEE CALLOUTS						A1		00779		C=206503			
CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1	
												REV AA	