

MATERIALS AND FINISHES






BODY AND COUPLUNG NUT STAINLESS STEEL
PASSIVATED

CENTER CONTACT BRASS
PLATED GOLD



INSULATOR TEFLON

CRIMP TUBE BRASS
PLATED NICKEL


SHRINK TUBE VERSIFIT OR EQUIVALENT



CONTACT



SHRINK TUBE



RECOMMENDED STRIP DIMENSIONS

LABEL FORMAT FOR
73251-0112

PART NUMBER: 73251-0111
ORDER NUMBER: 73251-0112
MOLEX
DATE: YYWW

73251-0112	ONE PIECE 73251-0111 PER BAG
73251-0111	BULK
PART NO.	PACKAGING

ES-89675-1570	CABLE ASSY INSTRUCT.
MIL-STD-348A, FIG. 310.1	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: UPDATE LABEL FOR -0112	EC NO: URF2012-0380 DRAWN BY: DRWNBOMALLEY CHKD BY: CHKD-AZR APPR: JWIENER	2012/01/04 2012/01/04 2012/01/04	DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
								MM/IN						
								DRAWN BY	DATE	TITLE				
						4 PLACES	± ---	± ---	GMH	1997/11/07	SMA PLUG, STR. CRIMP TYPE FOR RG55/142/223/400 SMA-PC			
						3 PLACES	± ---	± ---	CHECKED BY	DATE				
						2 PLACES	± ---	± ---	DHG	1998/01/05				
						1 PLACE	± ---	± ---	APPROVED BY	DATE				
						ANGULAR ± 2 °			GMH	1997/01/06				
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.	DOCUMENT NO.		SHEET NO.		
									SEE TABLE		SD-73251-011		1 OF 1	
									SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				