






Copyright FCI.

PRODUCT N°
SEE TABLE







REFERENCE PLAN DEFINED BY THE BEARING SURFACE

0.1
SEE NOTE 6




VACUUM AREA FOR 98432-X2XLF


POS.#1



98432-XX2



98432-XX3



98432-XX4

spec ref		-		dr		A Parrenin		2002/09/19		projection		mm		size		A3		scale		3:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		J Dalibard		2016/02/01						ecn no		ELX-B-16041-1			
±0.13						chr		J Dalibard		2016/02/01						rel level				Released	
±2°						appr		Aymeric Soudy		2016/02/08											
surface		linear		0.X		±Y				title		VERTICAL SMT 6 POSITIONS		dwg no		98432		rev		U	
				0.XX		±Y															
				0.XXX		±Y															
ISO 1302		angular		0°		±Y°		www.fci.com		cat. no.		98432-XXX(LF)		Product - Customer Drw		sheet 1 of 2					

VERTICAL SMT 6 POSITIONS

98432

U

