



Pushing Performance  
Since 1945

# M12 slim female crimp 8 pol A cod



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 821 2805
Specification	M12 slim female crimp 8 pol A cod
HARTING eCatalogue	<a href="https://b2b.harting.com/21038212805">https://b2b.harting.com/21038212805</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector
Specification	Straight

## Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded
Number of contacts	8
Coding	A-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 22
Wire outer diameter	≤1.65 mm
Rated current	2 A
Rated voltage	30 V AC 30 V DC
Rated impulse voltage	0.8 kV



**Pushing Performance**  
Since 1945

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521
	CSA-C22.2 No. 182.3 CYJV8.E302521

## Commercial data

Packaging size	1
----------------	---



**Pushing Performance**  
Since 1945

Commercial data

Net weight	46 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140225664
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)