






| LOC | DIST | REVISIONS |     |                           |         |      |
|-----|------|-----------|-----|---------------------------|---------|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN  |
| J   | —    |           | B1  | REVISED PER ECR-10-019980 | 04OCT10 | HMR  |
|     |      |           |     |                           |         | APVD |
|     |      |           |     |                           |         | TM   |




TYPE OF KEYING



注記  
1. 一般公差: ±0.3  
△ 材料PBTガラス強化(UL94V-0)  
△ かん合相手製品型番  
プラグハウジング: TABLE参照のこと  
タブコンタクト: 917764, 917765

NOTE  
1. GENERAL TOLERANCE: ±0.3  
△ MATERIAL: PBT GLASS FILLED (UL94V-0)  
△ MATING CONN. P/N  
PLUG HOUSING: SEE TABLE  
TAB CONTACT: 917764, 917765

断面 A-A  
SECT A-A



|                             |                           |                |                   |
|-----------------------------|---------------------------|----------------|-------------------|
| 4-1903388-2                 | TYPE B                    | BLACK<br>黒色    | 4-1903391-2       |
| 3-1903388-4                 | TYPE D                    | YELLOW<br>黄色   | 3-1903391-4       |
| 2-1903388-3                 | TYPE C                    | BLUE<br>青色     | 2-1903391-3       |
| 1-1903388-2                 | TYPE B                    | RED<br>赤色      | 1-1903391-2       |
| 1903388-1                   | TYPE A                    | NATURAL<br>自然色 | 1903391-1         |
| △ かん合相手型番<br>MATING HSG P/N | キーイング形状<br>TYPE OF KEYING | 色調<br>COLOR    | 型番<br>PART NUMBER |

|                                                                 |  |                                   |                 |                                                               |                    |
|-----------------------------------------------------------------|--|-----------------------------------|-----------------|---------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                          |  | DWN<br>J. SATO                    | 31OCT05         | Tyco Electronics AMP K.K.<br>Kawasaki, Japan                  |                    |
| DIMENSIONS:<br>単位: 耗<br>mm                                      |  | CHK<br>T. HATANO                  | 31OCT05         |                                                               |                    |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差               |  | APVD<br>N. YAMASAKI               | 31OCT05         | NAME<br>名称<br>GRACE INERTIA CONNECTOR 2.5 W<br>CAP HOUSING 2P |                    |
| 0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |  | PRODUCT SPEC<br>製品規格<br>108-78350 |                 |                                                               |                    |
| MATERIAL<br>材料<br>SEE NOTE △                                    |  | APPLICATION SPEC<br>取付適用規格        |                 | SIZE<br>A3                                                    | CAGE CODE<br>00779 |
| FINISH<br>仕上                                                    |  | WEIGHT                            |                 | DRAWING NO<br>番号<br>C-1903391                                 | RESTRICTED TO<br>— |
| CUSTOMER DRAWING                                                |  | SCALE<br>尺度<br>5:1                | SHEET<br>1 OF 1 | REV<br>B1                                                     |                    |