


SAI-M23-BE-L-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Pinning**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Insert
Order No.	1170370000
Type	SAI-M23-BE-L-6
GTIN (EAN)	4032248962266
Qty.	1 pc(s).

SAI-M23-BE-L-6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	8.5 g
------------	-------

Technical data customisable plug-in connectors

Coding	none	Housing main material	Thermoplastic polyamide PA 6, PBT
Number of poles	6	Plugging cycles	> 1000
Pollution severity	3	Rated current	20 A
Rated current	2 mm contact= 28 A	Rated voltage	600 V
Rated voltage	2 mm contact= 600 V	Type of connection	Crimp connection

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC003557
ETIM 8.0	EC003557	ECLASS 9.1	27-44-02-05
ECLASS 10.0	27-44-02-23	ECLASS 11.0	27-44-02-23
ECLASS 12.0	27-44-02-23		

Important note

Product information	Enclosures, inserts and crimp contacts need to be ordered separately.
---------------------	---

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads


Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-M23-BE-L-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Dimensioned drawing****Technical data**

No. of poles	5 + PE	4/4	
Number of contacts	6	4	4
Contact-ø	mm 2	1	2

6 times female, 2 mm