


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	26OCT2020	TL	HL

NOTE:
1. MATERIAL:
HOUSING: THERMOPLASTIC, UL94 V-0, COLOR: BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: [SEE TABLE]u" MIN. GOLD PLATING ON THE CONTACT AREA,
3.0um [120u"] MIN. MATTE-TIN ON SOLDER TAIL.
1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.



SECTION A-A


CONNECTOR LINK WIDTH	# PDS REF	DIM"A"	DIM"B"	DIM"C"	DIM"D"	DIM"E"	PCB THK REF.
X1	36P	9.15	25.00	6.00	7.65	2.30	1.58
X4	64P	23.15	39.00	20.00	21.65	3.10	2.36
X8	98P	40.15	56.00	37.00	38.65		
X16	164P	73.15	89.00	70.00	71.65		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 04SEP2019	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK ALEX SHOAL 04SEP2019				
		APVD HOPE LU 04SEP2019	NAME PCI EXPRESS CARD EDGE DIP TYPE GEN4 CONNECTOR			
		PRODUCT SPEC	-			
MATERIAL -		APPLICATION SPEC	-			
		WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C=2362375	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 4	REV A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—


30u"	3.10	164	5-2362375-4
	3.10	98	5-2362375-3
	3.10	64	5-2362375-2
	3.10	36	5-2362375-1
15u"	3.10	164	4-2362375-4
	3.10	98	4-2362375-3
	3.10	64	4-2362375-2
	3.10	36	4-2362375-1
G/F	3.10	164	3-2362375-4
	3.10	98	3-2362375-3
	3.10	64	3-2362375-2
	3.10	36	3-2362375-1
30u"	2.30	164	2-2362375-4
	2.30	98	2-2362375-3
	2.30	64	2-2362375-2
	2.30	36	2-2362375-1
15u"	2.30	164	1-2362375-4
	2.30	98	1-2362375-3
	2.30	64	1-2362375-2
	2.30	36	1-2362375-1
G/F	2.30	164	2362375-4
	2.30	98	2362375-3
	2.30	64	2362375-2
	2.30	36	2362375-1
GOLD PLATING	E	POS.	PART NUMBER

DATE CODE & P/N




2362375

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI	04SEP2019	 TE Connectivity Ltd.				
		CHK SANDERS YAN	04SEP2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PCI EXPRESS CARD EDGE DIP TYPE GEN4 CONNECTOR —				
		APVD HOPE LU						04SEP2019
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C-2362375	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 4:1	SHEET 2 of 4	REV A



CONNECTOR LINK WIDTH	# POS REF	N	DIM"B"	"C"
X1	36P	6.00	8.15	B17
X4	64P	20.00	22.15	B31
X8	98P	37.00	39.15	B48
X16	164P	70.00	72.15	B81




- 1 NO TIE BAR PERMITTED FROM CARD EDGE TO
LEADING EDGE OF PAD FOR PINS A1 AND "C".
- 2 CHAMFER EDGES MUST BE FREE OF CUTTING BURRS.
- 3 TOLERANCE: .xx ± 0.13 .




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI04SEP2019		 TE Connectivity Ltd.			
		CHK SANDERS YAN04SEP2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVDHOPE LU04SEP2019		NAME PCI EXPRESS CARD EDGE DIP TYPE GEN4 CONNECTOR —			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C-2362375	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1	SHEET 3 of 4	REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—


PRODUCT




TRAY





FIBER PAPER



TRAY





INNER BOX




OUTER BOX

DRIER 4PCS(1g/PC)



FOAM



4	X1	100	10	4	4000
3	X4	60	10	4	2400
2	X8	40	10	4	1600
1	X16	20	10	4	800
CODE	DESCRIPTION	PCS/TRAY	TRAY/INNER BOX	INNER BOX/OUTER BOX	PCS/OUTER BOX
			QUANTITY		

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TONY LI 04SEP2019		 TE Connectivity Ltd.						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK SANDERS YAN 04SEP2019							
		APVD HOPE LU 04SEP2019		NAME PCI EXPRESS CARD EDGE DIP TYPE GEN4 CONNECTOR							
		PRODUCT SPEC									
		APPLICATION SPEC									
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
-		-		WEIGHT 0		A2		00779		C=2362375	
CUSTOMER DRAWING						SCALE 4:1		SHEET 4 of 4		REV A	