

PLUG KIT PART NUMBER  
SEE TABLE 2 ON SHEET 2

OCTIS PLUG KIT, PoE, FIELD TERMINABLE, PITCH 26MM





TABLE 1

| SL NO. | COMPONENT               | QUANTITY | MATERIAL                          | REMARKS                                                   |
|--------|-------------------------|----------|-----------------------------------|-----------------------------------------------------------|
| 1      | PLUG CAP                | 1        | PBT GF                            | COLOR-BLACK                                               |
| 2      | CABLE CONNECTOR HOUSING | 1        | PBT GF                            | -                                                         |
| 3      | TERMINAL BLOCK ASSEMBLY | 2        | LCP,COPPER ALLOY                  | 8/10/12 POS.                                              |
| 4      | HOLDER SUBSET KIT       | 1        | ZAMAK(PASSIVATED),<br>SS,SILICONE | SCREW M2X12MM<br>RECOM.COUPLING<br>TORQUE-22 Ncm          |
| 5      | HOUSING SUBSET KIT      | 1        | PBT GF, IXEF                      | -                                                         |
| 6      | SPLIT RUBBER GLAND      | 1        | SILICONE                          | DIA 7MM *                                                 |
| 7      | TIGHTENING CONE         | 1        | PA                                | -                                                         |
| 8      | GLAND NUT               | 1        | PBT GF                            | COLOUR YELLOW<br>RECOM.COUPLING<br>TORQUE-2 MIN TO 2.5 Nm |


\* - STD RUBBER GLAND DIA OFFERED IS 7MM;OPTIONAL RUBBER GLAND  
DIA OF 8,9,10 AND 11.5MM ARE AVAILABLE ON REQUEST

|                                                    |  |                                       |  |       |  |                |  |                                    |  |                                   |  |                           |  |                        |  |           |  |              |  |               |  |     |  |   |  |
|----------------------------------------------------|--|---------------------------------------|--|-------|--|----------------|--|------------------------------------|--|-----------------------------------|--|---------------------------|--|------------------------|--|-----------|--|--------------|--|---------------|--|-----|--|---|--|
| spec ref                                           |  |                                       |  | dr    |  | Alosius, Stali |  | 2019/06/15                         |  | <div>projection</div> <div></div> |  | <div>mm</div> <div></div> |  | size                   |  | A3        |  | scale        |  | 1:1           |  |     |  |   |  |
| tolerance std                                      |  | TOLERANCES UNLESS OTHERWISE SPECIFIED |  |       |  | eng            |  | Alosius, Stali                     |  |                                   |  |                           |  | 2020/12/29             |  | ecn no    |  |              |  | ELX-I-38831-1 |  |     |  |   |  |
| ISO 406<br>ISO 1101                                |  |                                       |  |       |  | chr            |  | -                                  |  |                                   |  |                           |  | -                      |  | rel level |  |              |  | Released      |  |     |  |   |  |
|                                                    |  |                                       |  | appr  |  | Kuriakose, San |  | 2020/12/29                         |  | product family                    |  |                           |  | OCTIS                  |  |           |  |              |  |               |  |     |  |   |  |
| <div>surface</div> <div></div> <div>ISO 1302</div> |  | linear                                |  | 0.X   |  | ±0.3           |  | <div>Amphenol</div> <div>FCi</div> |  | title                             |  | OCTIS PLUG KIT, SIGNAL    |  |                        |  | dwg no    |  | 10135750     |  |               |  | rev |  | G |  |
|                                                    |  |                                       |  | 0.XX  |  | ±0.10          |  |                                    |  |                                   |  |                           |  |                        |  |           |  |              |  |               |  |     |  |   |  |
|                                                    |  |                                       |  | 0.XXX |  | ±0.050         |  |                                    |  |                                   |  |                           |  |                        |  |           |  |              |  |               |  |     |  |   |  |
|                                                    |  | angular                               |  | 0°    |  | ±2°            |  |                                    |  |                                   |  |                           |  |                        |  |           |  |              |  |               |  |     |  |   |  |
|                                                    |  |                                       |  |       |  |                |  |                                    |  | cat. no.                          |  | -                         |  | Product - Customer Drw |  |           |  | sheet 1 of 2 |  |               |  |     |  |   |  |

CONNECTOR FRONT VIEW  
(SHOWN 10135750-101LF)



PACKING CONFIGURATION



PACKING NOTE: UNITARY IN PLASTIC BAG WITH ASSEMBLY NOTE

TABLE 2

| AFCI PART NO                        | ROW | COLUMN1 | COLUMN2 | COLUMN3 |
|-------------------------------------|-----|---------|---------|---------|
| SIGNAL CONTACT LOADING POSITION     |     |         |         |         |
| 10135750-101LF                      | D   | X       | X       | -       |
|                                     | C   | -       | X       | X       |
|                                     | B   | X       | X       | -       |
|                                     | A   | -       | X       | X       |
| 10135750-102LF                      | D   | X       | X       | X       |
|                                     | C   | -       | X       | X       |
|                                     | B   | X       | X       | X       |
|                                     | A   | -       | X       | X       |
| 10135750-103LF                      | D   | X       | X       | X       |
|                                     | C   | X       | X       | X       |
|                                     | B   | X       | X       | X       |
|                                     | A   | X       | X       | X       |
| 10135750-104LF                      | D   | -       | X       | X       |
|                                     | C   | -       | X       | X       |
|                                     | B   | -       | X       | X       |
|                                     | A   | -       | X       | X       |
| X INDICATES CONTACT LOADED POSITION |     |         |         |         |

|                                      |                                       |         |        |                                                                                       |                                                                 |            |                                                                                       |                                                                                       |                            |                        |       |                 |              |
|--------------------------------------|---------------------------------------|---------|--------|---------------------------------------------------------------------------------------|-----------------------------------------------------------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------------|------------------------|-------|-----------------|--------------|
| spec ref                             |                                       |         |        | dr                                                                                    | Alosius, Stali                                                  | 2019/06/15 |  |  | size                       | A3                     | scale | 1:1             |              |
| tolerance std<br>ISO 406<br>ISO 1101 | TOLERANCES UNLESS OTHERWISE SPECIFIED |         |        | eng                                                                                   | Alosius, Stali                                                  | 2020/12/29 |                                                                                       |                                                                                       | ecn no                     | ELX-I-38831-1          |       |                 |              |
|                                      |                                       |         |        | chr                                                                                   | -                                                               | -          |                                                                                       |                                                                                       | rel level: <b>Released</b> |                        |       |                 |              |
|                                      |                                       |         |        | appr                                                                                  | Kuriakose, San                                                  | 2020/12/29 |                                                                                       |                                                                                       |                            |                        |       | product family  |              |
| surface<br>ISO 1302                  | linear                                | 0.X     | ±0.3   |  | title<br>OCTIS PLUG KIT, SIGNAL<br>FIELD TERMINABLE, PITCH 26mm |            |                                                                                       | dwg no                                                                                | 10135750                   |                        |       | rev<br><b>G</b> |              |
|                                      |                                       | 0.XX    | ±0.10  |                                                                                       |                                                                 |            |                                                                                       |                                                                                       |                            |                        |       |                 |              |
|                                      |                                       | 0.XXX   | ±0.050 |                                                                                       |                                                                 |            |                                                                                       |                                                                                       |                            |                        |       |                 |              |
|                                      |                                       | angular | 0°     | ±2°                                                                                   |                                                                 | cat. no.   |                                                                                       |                                                                                       | -                          | Product - Customer Drw |       |                 | sheet 2 of 2 |