





VERSION/Variante 0-1452388-2



FOR VERSION 0-1452388-2 ONLY / Nur fuer Variante 0-1452388-2		
NOTE Bem.	FEATURE Merkmal	Tyco Electronics - No.
2	APPLICATION SPECIFICATION Verarbeitungsspezifikation	114-18966
3	USEABLE RECEPTACLE HOUSING Passendes Buchsengehäuse	1563173




1:1

NOTES:
Bemerkungen

1 DELIVERY CONDITION: LOOSE PIECES
Anlieferungszustand: Teile lose beigestellt

0-1452388-2	PA66-GF25	96 POS. CON. 2-ndary LOCK	1.5	RED -	2
0-1452388-1	PA66-GF25	96 POS. CON. 2-ndary LOCK	1.6	RED -	1
TE ORDER NO.	MATERIAL	DESCRIPTION	WEIGHT [G]	COLOUR	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION DIESSES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ANGEHÖRIGEN UND/ODER ZUGEHÖRIGEN ANGESTELLTEN DER TYCO ELECTRONICS CORPORATION.		DWN K. ROTH 12MAR2002		Tyco Electronics AMP GmbH D - 64625 Bensheim	
DIMENSIONS: MASSE IN HEINEN: (MM)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEIN TOLERANZEN		CHN S. DENTER 12MAR2002	
		APVO G. MUMPER 12MAR2002		NAME 96 POS. CONNECTOR 2-ndry LOCK FOR 154 POS CON.	
		PRODUCT SPEC PRODUKTSPEZ. -		-	
		APPLICATION SPEC VERABREITUNGSSPEZ. -		-	
		SIZE A2		CAGE CODE 00779	
		DRAWING NO. ZEICHNUNGS-NR. C=1452388		RESTRICTED TO NUR FÜR -	
MATERIAL -		WEIGHT GEWICHT -		SCALE MASSSTAB 2:1	
FINISH/OBERFLÄCHE/FARBE -		CUSTOMER DRAWING /KUNDENZEICHNUNG		SHEET BLATT 1 OF 1	
				REV 2	