







P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED (ECR-20-001845)	07FEB2020	JH	YJ
	B	REVISED (ECR-20-015966)	04JAN2021	YH	YJ



SCALE 1:1



NOTES

1. GENERAL TOLERANCE : ± 0.5 , $\pm 3^\circ$
 2. CONDITION OF DELIVERY : DBL PLATE IN OPEN POSITION.
 3. APPLICABLE CONTACT P/N : 963774
 4. APPLICABLE SINGLE WIRE SEAL P/N : 1355437-2(COLOR : BLUE)
INSULATION DIAMETER : 5.8~6.6mm
 5. APPLICABLE PLUG ASS'Y P/N : 1743793
 6. INSERTION FORCE BETWEEN CONTACT AND HSG : MAX 7.5Kgf
- TE LOGO

ASS'Y P/N
1743797-1

2	NATURAL	PA66-GF15	DBL HSG	I
1	BLACK	PA66-GF15	CAP HSG	I
NO	FINISH/ COLOR	MATERIAL	DESCRIPTION	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YH MA	 TE Connectivity	
DIMENSIONS: mm		CHK YD LEE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD YJ YOUN		
3rd ANGLE PROJECTION		PRODUCT SPEC 108-61137 (A1)		
MATERIAL SEE TABLE		APPLICATION SPEC 411-61066 (A3)	NAME MCP 9.5mm IP CAP ASS'Y	
		WEIGHT	SIZE A3	
		CUSTOMER DRAWING	CAGE CODE 00779	
			DRAWING NO C-1743797	
			RESTRICTED TO -	
			SCALE 1:1	
			SHEET 1	
			OF 1	
			REV B	