


4

3


2

1

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005033	2APR11	RK	HMR






TYPE 1




TYPE 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10>	: ±0.2
30> * >10	: ±0.25
100> * >30	: ±0.3
ANGLE	: ±3°

NOTE:
1. PEELING STRENGTH: 0.20-0.69N (20-70gf)
PEELING ANGLE: 165-180°
PEELING SPEED: 300mm/MINUTE.



		DWN S.XU 31JAN03	 TE Connectivity	
DIMENSIONS: mm		CHK S.YAO 31JAN03	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED	
		APVD T.SASAKI 31JAN03		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± SEE L.H.S. 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-60018	SIZE A3 CAGE CODE 00779 DRAWING NO C-292230 RESTRICTED TO -	
MATERIAL -		APPLICATION SPEC 114-5223		
FINISH -		WEIGHT	SCALE NON SHEET 1 OF 4 REV B1	
		CUSTOMER DRAWING		

THIS DRAWING IS UNPUBLISHED.
ALL RIGHTS RESERVED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY

LOC	DIST	REVISIONS							
FB	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
				SEE SHEET 1					


	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BLACK	7-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		6-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		6-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		6-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		6-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		6-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		6-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		6-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		6-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		6-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		6-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		5-292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		5-292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		5-292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		5-292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		5-292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		5-292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		5-292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
		TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL		POS
DIMENSIONS													

	TYPE 2	49.5	45.5	6.2	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292230-0
		49.5	45.5	4.7	40.4	28.4	44	31.4		500	19		1-292230-9
		49.5	45.5	6.2	40.4	26.9	44	29.9		500	18		1-292230-8
		49.5	45.5	4.7	40.4	25.4	44	28.4		500	17		1-292230-7
		49.5	45.5	6.2	40.4	23.9	44	26.9		500	16		1-292230-6
		49.5	45.5	4.7	40.4	22.4	44	25.4		500	15		1-292230-5
		49.5	45.5	6.2	40.4	20.9	44	23.9		500	14		1-292230-4
		49.5	45.5	4.7	40.4	19.4	44	22.4		500	13		1-292230-3
		37.5	33.5	6.2	28.4	17.9	32	20.9	14.2	500	12		1-292230-2
		37.5	33.5	4.7	28.4	16.4	32	19.4	14.2	500	11		1-292230-1
		37.5	33.5	6.2	28.4	14.9	32	17.9	14.2	500	10		1-292230-0
		37.5	33.5	4.7	28.4	13.4	32	16.4	14.2	500	9		292230-9
	TYPE 1	29.5	25.5	6.2	-	11.9	24	14.9	11.5	500	8		292230-8
		29.5	25.5	4.7	-	10.4	24	13.4	11.5	500	7		292230-7
		29.5	25.5	6.2	-	8.9	24	11.9	11.5	500	6		292230-6
		29.5	25.5	4.7	-	7.4	24	10.4	11.5	500	5		292230-5
		21.5	17.5	6.2	-	5.9	16	8.9	7.5	500	4		292230-4
		21.5	17.5	4.7	-	4.4	16	7.4	7.5	500	3		292230-3
		21.5	17.5	2.8	-	2.9	16	5.9	7.5	500	2		-
TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N	
	DIMENSIONS												

DIMENSIONS: mm		DWN	MATERIAL	FINISH
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	 TE Connectivity	
0 PLC ±-		APVD		
1 PLC ±0.1		PRODUCT SPEC	NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH	
2 PLC ±0.01		SEE SHEET 1 OF 4	SINGLE ROW POST HDR ASS'Y (V)	
3 PLC ±0.001		APPLICATION SPEC	SMT TYPE WITH BOSS, EMBOSS TAPE PACKAGED	
4 PLC ±0.0001		SEE SHEET 1 OF 4	SIZE	RESTRICTED TO
ANGLES ±-		WEIGHT	CAGE CODE	A4 00779 C-292230
		CUSTOMER DRAWING	DRAWING NO	
SCALE NON			SHEET 2 OF 4	REV B1

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	7-292230-0	2-292230-0
0.93	30.0	31.0	29.1	27.0	19	6-292230-9	1-292230-9
0.89	28.5	29.5	27.6	25.5	18	6-292230-8	1-292230-8
0.84	27.0	28.0	26.1	24.0	17	6-292230-7	1-292230-7
0.80	25.5	26.5	24.6	22.5	16	6-292230-6	1-292230-6
0.75	24.0	25.0	23.1	21.0	15	6-292230-5	1-292230-5
0.71	22.5	23.5	21.6	19.5	14	6-292230-4	1-292230-4
0.66	21.0	22.0	20.1	18.0	13	6-292230-3	1-292230-3
0.62	19.5	20.5	18.6	16.5	12	6-292230-2	1-292230-2
0.57	18.0	19.0	17.1	15.0	11	6-292230-1	1-292230-1
0.52	16.5	17.5	15.6	13.5	10	6-292230-0	1-292230-0
0.48	15.0	16.0	14.1	12.0	9	5-292230-9	292230-9
0.43	13.5	14.5	12.6	10.5	8	5-292230-8	292230-8
0.39	12.0	13.0	11.1	9.0	7	5-292230-7	292230-7
0.34	10.5	11.5	9.6	7.5	6	5-292230-6	292230-6
0.30	9.0	10.0	8.1	6.0	5	5-292230-5	292230-5
0.25	7.5	8.5	6.6	4.5	4	5-292230-4	292230-4
0.20	6.0	7.0	5.1	3.0	3	5-292230-3	292230-3
0.17	4.5	5.5	3.6	1.5	2	-	-
WEIGHT (g)	D	C	B	A	Pos.	BLACK	BEIGE (NAT)
	DIMENSIONS					P/N	

DIMENSIONS: mm		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		MATERIAL SEE SHEET 1		FINISH SEE SHEET 1	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±				 TE Connectivity			
				NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS			
				SIZE A4	CAGE CODE 00779	DRAWING NO C-292230	RESTRICTED TO
CUSTOMER DRAWING				SCALE NON	SHEET 4	OF 4	REV B1