


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	J	REVISED PER ECO-18-000969	23JAN2018	RS	MZ



1 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.

2 WILL ACCEPT (28) SIZE 20 SOCKET CONTACTS.

3 PART NUMBER AND DATE CODE MARKED ON ANY FLANGE EDGE.

4 PART NUMBER AND DATE CODE MARKED ON ANY FLANGE EDGE OR TOP OF FLANGE.

206038-4

206038-2

206038-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.STAUB BG 4/5/91	TE Connectivity Ltd.			
DIMENSIONS: INCHES		CHK W.G.LENKER 7-24-92				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH -		APVD K.BEAVER 7-24-92 PRODUCT SPEC 108-10024 APPLICATION SPEC -			
MATERIAL THERMOPLASTIC, BLACK		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=206038	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV J	