

Material

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Side Contact pin : PhBz Tin plated.
- Item ③ Center contact pin: PhBz.Tin plated.
- Item ④ Terminal lever : Thermoplastic (UL94V-0)
- Item ⑤ Terminal cover : Thermoplastic (UL94V-0)

⚠ Electrical: cULus CQC

⚠ ● Voltage rating: 300V 300V

● Current rating: 2A 2A

● Wire range:

● Solid wire(AWG): 20-26 20

● Stranded wire(AWG): 20-26 20

⚠ ● Wire strip length: 8.5-10.0mm

● Withstanding Voltage: 1.6KV 2.5KV

⚠ ● Operating temperature: -40℃ to +115℃

● The soldering temperature: 250℃±5℃/5 Sec.

⚠ ● Safety Approval:  

⚠ HC xx B 2 x 0 xxxx G ⚠

OF POLES ————

2: 2 POLES

:

:

+: 24 POLES

OR ————

Red

Orange

Green (RAL 6018/T)

Grey (RAL 7004/P)

0000: “@” Logo (Standard)

000A: “ANYTEK” Mark

Any special item by customer request.

please contact sales department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	HC 2.5mm -High profile Series						
PART NO.	HCxxB2x0xxxxG			DWG NO.	8HC0501		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Runner 2010.12.25	Tony 2008.09.16			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: E	X.XX ±0.10
							X° ±1°