



| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| GP  | 00   |           | P   | REVISED PER ECO-11-004835 | 11MAR11 | RK  | HMR  |



- 1 SCREW: CARBON STEEL.  
MOUNTING SCREW & HEX NUT: CARBON STEEL.  
CABLE CLAMP: ZINC.
- 2 SCREWS, MOUNTING SCREWS & HEX NUTS: ZINC PLATE 5.08µm-10.16µm  
[.000200-.000400] THICK, CLEAR CHROMATE COATING.  
CABLE CLAMP: 5.08µm [.000200] MIN NICKEL  
OVER 5.08µm [.000200] MIN COPPER.

**COPYRIGHT 2005**  
**TE CONNECTIVITY CORP**  
**ALL RIGHTS RESERVED**

|                   |              |           |
|-------------------|--------------|-----------|
| I                 | 9.53 [.375]  | 5745175-6 |
| L                 | 11.43 [.450] | 5745175-5 |
| O                 | 13.34 [.525] | 5745175-4 |
| S                 | 15.24 [.600] | 5745175-3 |
| U                 | 17.15 [.675] | 5745175-2 |
| V                 | 19.05 [.750] | 5745175-1 |
| NECK<br>SIZE I.D. | CABLE<br>DIA | PART NO.  |

|                                                                                       |  |                                |                                                                                           |              |                 |          |
|---------------------------------------------------------------------------------------|--|--------------------------------|-------------------------------------------------------------------------------------------|--------------|-----------------|----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>D. HENNY<br>8-13-05     | TE Connectivity                                                                           |              |                 |          |
| DIMENSIONS:<br>MM[INCHES]                                                             |  | CHK<br>C. ROHDE<br>8-13-05     |                                                                                           |              |                 |          |
|                                                                                       |  | APVD<br>M. WALMSLEY<br>8-13-05 | NAME<br>CABLE CLAMP KIT, UNASSEMBLED,<br>SIZE 5, 50 POSITION, 180DEG,<br>AMPLIMITE SERIES |              |                 |          |
|                                                                                       |  | PRODUCT SPEC                   |                                                                                           |              |                 |          |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                             |  | APPLICATION SPEC               | SIZE<br>A2                                                                                |              |                 |          |
| 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± .013 [.005]<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |  | FINISH                         |                                                                                           |              |                 |          |
| MATERIAL                                                                              |  | WEIGHT                         | CAGE CODE                                                                                 | DRAWING NO   | RESTRICTED TO   |          |
| 1                                                                                     |  | 2                              | 00779                                                                                     | C=5745175    | -               |          |
| CUSTOMER DRAWING                                                                      |  |                                |                                                                                           | SCALE<br>2:1 | SHEET<br>1 of 1 | REV<br>P |