





NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER PLATED
5. CONTACT RATING: 125V AC 0.3A
6. OPERATING FORCE: 800 ± 300 g-cm
7. OPERATING TEMP: -30°C to 85°C
8. CIRCUIT SP: 10 POSITION 30° INDEX
9. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCK WASHER, HEXNUT, STOP RING
- ▲ 11. ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100585	Release	12/01/21	MW	TITLE KC50A9.501NLS				100120115
					SCALE	DATE	DR	DWG	REV
					3:2	11/30/2021	MW	G527973	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED