

- 1

SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

50 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

FLASH Au PLATING OVER Ni PLATING OVER Cu PLATING
- 4

0.8μm Au PLATING OVER Ni PLATING OVER Cu PLATING
- 5

Ni PLATING OVER Cu PLATING
- 6

TIN PLATING
- 7

RECOMMENDED SELF-TAPPING SCREW 221108-4
- 8




RECOMMENDED MOUNT NUT 1-1634816-0
- 9

RECOMMENDED LOCKWASHER 1-1634817-0
- 10

FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
- 11

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED
- 12

OBSOLETE



QUANTITY PER ASSY										PARTS LIST		
1	-	-	-	-	-	-	-	-	STEEL	5	LOCK WASHER	9
1	-	-	-	-	-	-	-	-	BRASS	5	NUT	8
-	-	-	-	-	2	2	-	-	BRASS	6	BOARD LOCK	7
2	2	2	-	-	-	-	2	2	BRASS	6	MOUNTING POST	6
1	1	1	1	1	1	1	1	1	BRASS	6	SOLDER TAIL	5
1	1	1	1	1	1	1	1	1	PE-606	4	INSULATOR	4
1	1	1	1	1	1	1	1	1	ZINC ALLOY	5	BODY	3
-	1	1	-	-	-	-	-	-	BRASS	4	CONTACT	2
1	-	-	1	1	1	1	1	1	PHOSPHOR BRONZE	3	CONTACT	1
1--4	6--3	1--3	6--2	1--2	6--1	1--1	6--0	1--0	MATERIAL		DESCRIPTION	ITEM
1	2	1	2	1	2	1	2	1				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5

1 PLC ± 0.3

2 PLC ± 0.2

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

SEE TABLE

DWN

RITA ZUO

14 Feb 09

CHK

ANSON MA

14 Feb 09

APVD

BOB ZHAO

14 Feb 09

PRODUCT SPEC

108-112000

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

BNC R/A PCB SHIELDED SOCKET 50 OHM

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1337494

RESTRICTED TO

-

SCALE

NTS

SHEET

1 of 1

REV

F2