







NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD
5. CONTACT RATING: 150mA, 250VAC/DC
350mA, 110VAC/DC
6. OPERATING FORCE: 0.8 ± 0.3 kg-cm
7. OPERATING TEMP: -30°C to 85°C
- ▲ 8. CIRCUIT DP: 6 POSITION 30° INDEX (NO STOPS)
9. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER and HEX NUT
11. ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-101363	Release	11/04/22	MW	TITLE KC20A13.001NLF				100123001
					SCALE	DATE	DR	DWG	REV
					3:2	11/3/2022	MW	G527575	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED