





- NOTES:
- 1 MATERIAL CONTACT; PHOSPHORBRONZE
 - 2 MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY) UL-RATING 49V0
 - 3 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND COMPLIANT PIN SECTION: 0,5µm TIN MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - 5 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - 6 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - 7 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
 - 8 CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
 - 9 CONNECTOR MARKED WITH PARTNUMBER AND DATECODE. THE MARKING CAN APPEAR ON THE FRONT SIDE OR ON THE BACK SIDE.
 - 10 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID. 110 HOLES.
 - 11 FITS WITH INTEGRATED GROUND RETURN UPPERSHIELD, BASIC P.N. 5338107 AND INTEGRATED GROUND RETURN LOWERSHIELD, BASIC P.N. 5338108
 - 12 AREA RESERVED FOR CODING KEY, BASIC P.N. 100526
 - 13 CONNECTOR ASSEMBLED WITH ALTERNATE FEMALE CONTACTS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.van Hoek 23-AUG-07	Tyco Electronics Corporation	
DIMENSIONS: mm		CHK B.Mooij 23-AUG-07	's-Hertogenbosch, 5222AR-32	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.Broeksteeg 23-AUG-07	NAME	
6-PLC ±		PRODUCT SPEC	Z-PACK 2mm HM TYPE A	
1-PLC ±		APPLICATION SPEC	110 POS. FEMALE CONNECTOR	
2-PLC ±		108-19082	-	
3-PLC ±		114-19029	-	
4-PLC ±		WEIGHT -	-	
ANGLES ±		CUSTOMER DRAWING	-	
FINISH -		SCALE 5:1	SHEET 1 OF 1	
-		REV C	-	

FINISH	MATERIAL	PARTNUMBER
2 6	1	1-1857989-9
2 5	1	1857989-9
2 4	1	1857989-4
2 3	1	1857989-1

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1857989	-