






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: x.x = ± 0.4
x.xx = ± 0.25
3. TERM. NUMBERS FOR REF ONLY
4. RATING: 50 MILLI-AMPS @24VDC
5. TRAVEL: 1.0 +/-0.5mm
6. CONTACT RESISTANCE: 30 MILLIOHMS MAX
7. INSULATION RESISTANCE: 10M OHMS MIN. AT 100VDC
8. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE
9. OPERATING FORCE: 300 $\pm$ 75gf
- ▲ 10. PACKAGING: TUBE, 45 PIECES PER TUBE
11. LIFE CYCLES: 10,000,000 ACTUATIONS
12. ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. ACTUATOR IS TO BE SHIPPED IN A PLASTIC BAG SEPARATE FROM THE SWITCH AND IS TO BE ASSEMBLED AFTER SOLDERING.



▲ ACTUATOR
COLOR: BLACK
(SEE NOTE 13)



▲ ACTUATOR (CAP) AND SWITCH ARE SHOWN ASSEMBLED FOR REFERENCE ONLY.
(SEE NOTE 13)



B	23942	Actuator to be shipped in bulk, add note 13	6/18/19	MW
A	23058	RELEASE FOR PRODUCTION	10/31/17	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL6200GBF300QP (SWITCH AND ACTUATOR)				
SCALE 2:1	DATE 10/31/2017	DR MW	DWG T060011	REV B