





1. WILL ACCEPT (12) MULTIMATE AND (4) TYPE XII PIN CONTACTS.

2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.

3. NO. 4 FASTENERS RECOMMENDED FOR MOUNTING.

4. THIS CONNECTOR WILL ACCEPT INSULATION DIAMETERS UP TO 3.81 [.150].

5. HOUSING: NYLON, BLACK.

6. PERIPHERAL SEAL: ELASTOMER, BLACK.

7. THREADED INSERT: BRASS

8. PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.

9. HOUSING: NYLON, RED.

10. PERIPHERAL SEAL: ELASTOMER, GRAY.

11. WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

12. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

OBsolete	5	#4-40 THREADED INSERTS	NO	A	1-207486-2
OBsolete	5	3.81+/- .08 (.125+/- .003) HOLES	YES	A	1-207486-1
OBsolete	7	3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-9
PRELIMINARY	6	3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-7
	5	#4-40 THREADED INSERTS	YES	A	207486-6
	5	3.81+/- .08 (.125+/- .003) HOLES	YES	A	207486-5
	5	3.81+/- .08 (.125+/- .003) HOLES	NO	B	207486-2
	5	3.81+/- .08 (.125+/- .003) HOLES	NO	A	207486-1
NOTES		MOUNTING FEATURES	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13 [.005]

3 PLC ± -

4 PLC ± -

ANGLES

FINISH

5

6

DWN M. BINNER 05/26/94

CHK R. STONE 6-23-94

APVD -

NAME

PRODUCT SPEC 108-10024

APPLICATION SPEC

SIZE CAGE CODE DRAWING NO

WEIGHT

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC

RESTRICTED TO

SCALE 2:1 SHEET 1 OF 1 REV U