






Material

- Item ① Terminal body (Contact pin): Brass, Tin plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Pull force:
- Screw:
- Wire strip length: 5-6mm
- Withstanding Voltage: 16KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 
- Critical dimension: 

HG XX 10 X 0 xxxx G

- 02 2 CONTACTS
- 03 3 CONTACTS
- 12 12 CONTACTS

- Color 
 - 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors
- 000 0 Standard @ Logo
 - 000 A Standard ANY Logo(lead<4%)
 - Any special item by customer request
 - In copper Alloy
 - please contact sales department.

Dimension

DIM A	(N-1)×10.0±5.9
DIM B	(N-1)×10.0

N=Number of poles

POLES	DIM B	DIM A
2p-4p	±0.15	±0.20
5p-7p	±0.20	±0.25
8p-10p	±0.25	±0.30
11p-12p	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM OR MANNER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		DWG NO.		Tolerance	
HG 10.0mm Series		8HG04.01		X. ±0.50	
PART NO.	HGx10x00000G	CUST NO.		X.X ±0.30	
CHECKED	DESIGNED	DRAWN		X.XX ±0.10	
APPROVED	Da cheng 2013.04.11	Da cheng 2013.04.11		X° ±1°	
SHEET: 01/01		REV.: F			

PCB LAYOUT
Bottom view

