

Coaxial Panel Connector 22_MCX-50-0-2/111_N

Description

Straight bulkhead receptacle jack

Interface standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Number of matings	500
Weight	0.0015 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)

Related Documents

Outline drawing	DOU-00010854
Catalogue drawing	DCA-00010691
Mounting hole	DOU-00008855

Ordering Information

Bulk 100 pcs package	22_MCX-50-0-2/111_NH
Single package	22_MCX-50-0-2/111_NE