




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

© COPYRIGHT — By —




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

RJ11 PREVENTER



DATA CODE



NOTE:

1. MATERIAL:

1.1 HOUSING: PA46, WITH 30% GF, UL94 V-0, BLACK COLOR.

1.2 INSERT HOUSING: PA46, WITH 30% GF, UL94 V-0, BLACK COLOR.

1.3 CONTACTS: PHOSPHOR BRONZE.

2. FINISH:

2.1 CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA.




GOLD FLASH ON SOLDER TAIL.

1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.

2.2 SHELL: 0.508um [20u"] MIN. NICKEL PLATED OVERALL.

3. WAVE SOLDER CAPABLE TO 265°C

PER TE SPEC 109-202, CONDITION B.



RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS: 1.6mm
TOLERANCE: ±0.05 (TOP VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± —
	1 PLC ± 0.3
	2 PLC ± 0.2
	3 PLC ± 0.15
	4 PLC ± —
	ANGLES ± 3°
MATERIAL	FINISH
—	—

DWN	B. HSING	20JUL2009
CHK	S. CHIEN	20JUL2009
APVD	W. KODAMA	20JUL2009
PRODUCT SPEC	108-57779	
APPLICATION SPEC	—	
WEIGHT	—	
CUSTOMER DRAWING		

2.39	3.5	W/O	1.27um[50u"]	1-2041035-5
2.37	2.2	W/O	1.27um[50u"]	1-2041035-4
WEIGHT (gram)	DIM N	SHELL	MIN. GOLD THICKNESS	PART NUMBER



TE Connectivity

NAME				
MODULAR JACK CONNECTOR RJ45, 8P8C, TAB DOWN SIDE ENTRY, DIP TYPE, H=11.3MM				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C-2041035	—	
SCALE		SHEET	REV	
1:1		2 OF 3	B	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT

By

SEE SHEET 1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

NOTES:

1. MATERIAL:

1.1 TRAY: PET

1.2 TOP TRAY: PET

1.3 AIRTIGHT BAG: PET

1.4 CARTON: CORRUGATED FIBER.

2. DIMENSION: SEE DRAWING

3. QUANTITY: SEE TABLE

4. WEIGHT: SEE TABLE

TOP COVER

LABEL

DETAIL C

SEE DETAIL C

TRAY

170

290

16

20 DESICCATING AGENTS AT LEAST

BAG

11 LAYERS*3

BOX

560

210

310

LABEL

10.2 Kg	7.1 Kg	33	90	2970	1-2041035-5
					1-2041035-4
13.8 Kg	10.7 Kg				2041035-5
					2041035-4
13.6 Kg	10.5 Kg	33	80	2640	2041035-3
					2041035-2
					2041035-1
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ BOX	PCS/ BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

± —

± 0.3

± 0.2

± 0.15

± —

± 3°

MATERIAL

—

FINISH

—

DWN

B. HSING

20JUL2009

CHK

S. CHIEN

20JUL2009

APVD

W. KODAMA

20JUL2009

PRODUCT SPEC

108-57779

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

STE

TE Connectivity

NAME

MODULAR JACK CONNECTOR

RJ45, 8P8C, TAB DOWN

SIDE ENTRY, DIP TYPE, H=11.3MM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041035

—

SCALE

1:1

SHEET

3 OF 3

REV

B

1470-19

(1/15)