


THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG		RELEASED FOR PUBLICATION FREI FUER VEROEFFENTLICHUNG		,19--		MATED WITH: PASSEND ZU:		LOC		DIST		REVISIONS ÄNDERUNGEN									
© COPYRIGHT 19--		BY AMP INCORPORATED.		ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN		-		A1		-		P	LTR	DESCRIPTION BESCHREIBUNG		DATE	DWN	APVD			
								PROJEKT NR.:				A2		NEW DRAWING CREATED		02APR02		M.P.	M.Dg.		
												A3		ECR-22-141001		31MAY2022		BV		GB	



A2	10	-	-	-	1355437-4	Silopren LSR 3186/50 704658-1/-2	-	RAL 9010 or similar (Pure white)
	10,8	7,1-8,1	16	967591	1355437-3	Silopren LSR 3286/50 704813-1/-2	A	RAL 3011 or similar (Brown red)
	10	5,8-6,6	10	967590	1355437-2	Silopren LSR 3186/50 704658-1/-2	A	RAL 5015 or similar (Sky blue)
	10	4,6-5,2	6	967590	1355437-1	Silopren LSR 3186/50 704658-1/-2	A	RAL 4006 or similar (Traffic purple)
	A (mm)	ISO-φ (mm2)	DGB (mm2)	USED WITH CONTACT	PART NO	MATERIAL	REV	COLOUR
PARTING LIST								

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT.
ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN.
DEN JEWELN LETZTQUELTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.

DIMENSIONS:
DIMENSIONEN:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN
n. ISO 8015
n. ISO 2768 - mH -E
n. DIN 16901 - 140
0 PLC ±0.3
1 PLC ±0.3
2 PLC ±
3 PLC ±-
ANGLES /WINKEL ±-
FINISH /OBERFLÄCHE/FARBE

DWN 03-APR-02
Pfeilschifter, M.

CHK 03-APR-02
Dangelmaier, M.

APVD 03-APR-02
Bleicher, M.

APPLICATION SPEC
VERARBEITUNGSSPEZ.

WEIGHT
GEWICHT 2.2g

CUSTOMER DRAWING /KUNDENZEICHNUNG

AMP tyco Electronics AMP GmbH
D - 64625 Bensheim

SINGLE WIRE SEAL FOR AMP MCP 9.5mm
Einzeldichtungen für AMP MCP 9.5mm

SIZE CAGE CODE DRAWING NO
ZEICHNUNGS-NR.
A3 00779 C-1355437

RESTRICTED TO
NUR FUER

MASSSTAB 5:1 BLATT 1 OF 1 REV A3