


| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | A   | RELEASE PER ECR-19-000700 | 16JAN2019 | JS  | DD   |
|   | A1  | REVISED PER ECR-19-003367 | 05MAR2019 | SR  | DD   |
|   | A2  | REVISED PER ECR-19-008525 | 31MAY2019 | SR  | DD   |
|   | A3  | REVISED PER ECR-20-002559 | 26FEB2020 | SB  | DD   |



- 1
- MATERIALS:  
HOUSING: PBT  
LINE VOLTAGE CONTACTS: COPPER ALLOY  
SHORTING CLIP: COPPER ALLOY  
GASKET: NBR/PVC BLEND  
O-RING: SILICONE RUBBER  
COVER: PBT, UL UV-f1 RATED
- 2
- FINISH:  
LINE VOLTAGE CONTACTS: MATTE TIN PLATE
- 3
- MATING INTERFACE PER ANSI C136.10.
- 4
- ADHESIVE BACKED GASKET APPLIED
5.
- THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 6
- PRODUCT INFORMATION LABEL
- 7
- 157 JOULE MOV WITH A MAX SURGE CURRENT OF 4500A AND A MAX CLAMPING VOLTAGE OF 1355V.

|           |                               |           |
|-----------|-------------------------------|-----------|
| RED       | OPEN                          | 2328118-3 |
| BLACK     | SHORTING AND SURGE PROTECTION | 2328118-2 |
| BLACK     | SHORTING                      | 2328118-1 |
| CAP COLOR | DESCRIPTION                   | PART NO.  |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
C. DAILY  
CHK  
M. STOLLER  
APVD  
-

23JAN2018  
23JAN2018

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±  
1 PLC ±0.2  
2 PLC ±0.13  
3 PLC ±  
4 PLC ±  
ANGLES ±1°  
FINISH -

MATERIAL  
SEE TABLE  
-

PRODUCT SPEC  
108-133113

APPLICATION SPEC  
408-133113

WEIGHT  
-

CUSTOMER DRAWING

NAME  
ASSEMBLY,  
LUMAWISE SHORTING CAP  
-

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C-2328118

RESTRICTED TO  
-

SCALE  
7:4

SHEET  
1

OF  
1

REV  
A3

TE Connectivity

TE