

Han 3M-HBM-SL-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 003 0305
Specification	Han 3M-HBM-SL-C
HARTING eCatalogue	https://b2b.harting.com/09370030305

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® M
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight With metal cover

Version

Size	3 A
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Details	for male inserts
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)



Pushing Performance
Since 1945

Material properties

Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	64.88 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140055186
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors