

R 15-EGW-13,5



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0102
Specification	R 15-EGW-13,5
HARTING eCatalogue	https://b2b.harting.com/09150000102

Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Angled

Version

Locking type	Screw locking
--------------	---------------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate (PC)
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Lead
	Naphthalene

Commercial data

Packaging size	10
Net weight	29.16 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors