




- NOTES:
1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
 2. TERMINAL FINISH:
SELECTED GOLD ON CONTACT AREA
GOLD FLASH ON SOLDER TAILS.
 3. PRODUCT SPEC: GS-12-629
 4. PACKAGE SPEC: GS-14-1517
 5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 10 SECONDS IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
 6. MATING SIDE LENGTH: 2.5mm MIN.
 7. PRODUCT NUMBERING:
20021814 -XXX XX X X LF

- LEAD FREE
- PLATING
 - 1: GOLD FLASH ON CONTACT AREA
 - 4: 10u" GOLD ON CONTACT AREA
 - 8: 30u" GOLD ON CONTACT AREA
- PACKING STYLE
 - T: TUBE
- PIN COUNT
 - 04, 06, 08 ... 98, A0
- STACK HEIGHT "K"
 - EXAMPLE: 045=4.5mm
 - IN 0.5mm INCREMENT


$$\frac{\text{Recommended P.C.B. Layout}}{\text{Layout Tolerance}} = \pm 0.05\text{mm}$$
[illegible]