







VIEW D
ROTATED


SECOND LOCKING DEVICE
IN PRE-LOCKED POSITION




SECOND LOCKING DEVICE
IN LOCKED POSITION



SECTION F-F



CLOSED CAVITY OF THE
2POS./3POS. SOCKET HOUSING



- 1 TYCO LOGO AND TYCO NUMBER OF SINGLE PART
- 2 MATERIAL MARKING, EXCHANGEABLE
- 3 REVISION OF THE MOULD
- 4 PRODUCTION DATE
- 5 CAVITY MARKING
6. FITS TO CONNECTORS ACC. TO DIN 72585/ISO 15170 FORM A AND B AND PIN-HOUSING 2-4POS. TYCO-PN 967402
7. FOR SUITABLE CONTACTS SEE DRAWING TYCO-PN: 1355065
MAX. WIRE THICKNESS: 2.5mm FLR
FOR SUITABLE SEALS SEE DRAWING: TYCO-PN: 1355070
8. BULK PACKING IN CARDBOARD BOX
- 9 CODING ACC. TO DIN 72585/ISO 15170
- 10 SECONDARY LOCK IS ONLY AVAILABLE FOR 1-1813099-X, 2-1813099-X, 3-1813099-X, 4-1813099-X. DETAIL SEE TABLE.

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG NO A_ZHANG	03JUN2005		
DIMENSIONS: mm		CHECKED BY R_ZHOU	250C12005		
 TOLERANCES UNLESS OTHERWISE SPECIFIED: % GENERAL TOLERANCE % HOLE % SHAFT PRODUCT SPEC 108-101006 APPLICATION SPEC 114-18255-0 ANGLES 10:00D1 FINISH #1.00"		NAME 2.5mm SOCKET CONNECTOR.2-4POS WITH SECONDARY LOCKING -			
		SIZE CASE CODE DRAWING NO RESTRICTED TO A100779 C=1813099			
		WEIGHT -			
		SCALE 3:1 SHEET 1 OF 1 REV A2			
MATERIAL SEE TABLE					