





FRAME

2-B
LOCKING

2-B
LOCKING

SCHEMATIC



NOTES:

- MATERIALS:
 - FRAME - STEEL, NICKEL PLATED
 - SPRINGS - SPRING TEMPERED, NICKEL SILVER
 - BUSHING & SHAFT - BRASS, NICKEL PLATED
 - INSULATION - PHENOLIC
 - CONTACTS - FINE SILVER
 - SCREWS - STEEL, NICKEL PLATED
 - SHAFT INSULATOR - NYLON
 - TUBING - THERMOPLASTIC
 - KNURLED NUT - BRASS, NICKEL PLATED
- ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: 20 MILLIOHMS MAX
 - CONTACT RATING: 3A, 300W MAX AC NON-INDUCTIVE LOAD
 - LEAKAGE RESISTANCE: 1000 MEGAOHMS OR GREATER
 - DIELECTRIC STRENGTH: 250 VDC
- HARDWARE SHIPPED UNASSEMBLED.
- THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH SPEC No.						MATERIAL SPEC No.					
						FIRST USED ON				SCALE 2:1		Switchcraft®					
						DATE DRAWN 03/10/10	BY RS	CHKD RS 03/10/10		APVD TJK 06/16/20							
A	25997	11/07/08	PC	TJK								SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD	NAME RIGHT-ANGLE LEVER SWITCH 3 POSITION LOCKING, RoHS						PART No. 12015X						REV A
REVISIONS					DO NOT SCALE DRAWING												