




D


C

B

A



SECTION A—A



RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	±	—
1. PLC	±	—
2. PLC	±	0.13 [.005]
3. PLC	±	—
4. PLC	±	—
ANGLES	±	—

SEE TABLE

DWN
R BROWN
CHK
K WRIGHT
APVD
K WRIGHT

09FEB01
09FEB01
09FEB01

NAME
HDR ASSY, RTANG, SR
2.54 [.100] CL, 0.64 [.025] SQ POST,
—

PRODUCT SPEC
108-25034

APPLICATION SPEC
114-25026

WEIGHT
—

CUSTOMER DRAWING

SIZE
A1

CAGE CODE
00779

DRAWING NO
103672

RESTRICTED TO
—

SCALE
4:1

SHEET
1 OF 2

REV
AF1

