








HOUSING

CONTACT
3 PLC




COVER




24.59±0.25
[.968±.010]

RECOMMENDED PANEL CUTOUT

- CONTACTS TO ACCEPT 14 AWG AND 12 AWG SOLID COPPER WIRE OR 14 AWG STRANDED WIRE WHEN USED WITH AMP 205 SERIES FASTON™ TAB.
- COVER PACKAGED UNASSEMBLED.
- SNAP IN FEATURE ACCOMODATES 0.76-1.78 [.030-.070] PANEL THICKNESS ONLY.
- ALL HOUSINGS AND COVERS ARE UL 94V-2 RATED UNLESS OTHERWISE SPECIFIED.
- UL 94V-0 RATED HOUSING AND COVER.



26.92±0.38
[1.060±.015]




24.26 MAX
[.955]

5.21 MAX
[.205]

3


CHARACTERS 402400022
MOLDED THIS SIDE
208979-1 ONLY



24.33 MAX
[.958]

25.15 MAX
[.990]

30.35 REF
[1.195]



ASSEMBLED VIEW

OBSOLETE	-	1-208979-5
	PUTTY WHITE	1-208979-4
OBSOLETE	BLACK	5 1-208979-3
	ORANGE	1-208979-2
	GRAY	1-208979-1
	GRAY	1-208979-0
OBSOLETE	CREAM	208979-9
OBSOLETE	WHITE	208979-7
	ALMOND	208979-4
	BLACK	208979-2
OBSOLETE	BLACK	208979-1
	HOUSING COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MOYER 5-1-91	TE Connectivity		
		CHK R STONE 5-7-91			
DIMENSIONS: mm[INCHES]		APVD D L ROCKER 5-7-91	NAME		
		PRODUCT SPEC	RECEPTACLE KIT, UNASSEMBLED, WITH COVER, CONVENIENCE OUTLET		
		APPLICATION SPEC			
MATERIAL		WEIGHT -	SIZE CAGE CODE DRAWING NO		RESTRICTED TO
HOUSING: NYLON, SEE TABLE COVER: NYLON BLACK CONTACTS: BRASS		FINISH -	A2 00779 C-208979		-
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV Y1