




| REVISIONS |     |                       |           |     |      |
|-----------|-----|-----------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION           | DATE      | DWN | APVD |
|           | A   | RELEASE TO PRODUCTION | 02APR2020 | AY  | PS   |
|           | A1  | 34 POSITION ADDED     | 11MAR2021 | AY  | PS   |
|           |     |                       |           |     |      |
|           |     |                       |           |     |      |



- NOTES:
1. MATERIAL:  
LCP BLACK, UL94 V0
  2. N = NUMBER OF POSITION PER HOUSING.
  3. HOUSING TO BE USED WITH CRIMP CONTACTS  
2316113 (AWG 28-24/0.08-0.22 mm<sup>2</sup>) AND  
2316114 (AWG 30-28/0.05-0.08 mm<sup>2</sup>)
  4. PACKAGING : BULK BOX



| BOX PACKAGING |         |    |
|---------------|---------|----|
| 5-2316109-0   | 50.1    | 50 |
| 4-2316109-4   | 44.1    | 44 |
| 4-2316109-0   | 40.1    | 40 |
| 3-2316109-4   | 34.1    | 34 |
| 3-2316109-2   | 32.1    | 32 |
| 3-2316109-0   | 30.1    | 30 |
| 2-2316109-8   | 28.1    | 28 |
| 2-2316109-6   | 26.1    | 26 |
| 2-2316109-4   | 24.1    | 24 |
| 2-2316109-2   | 22.1    | 22 |
| 2-2316109-0   | 20.1    | 20 |
| 1-2316109-8   | 18.1    | 18 |
| 1-2316109-6   | 16.1    | 16 |
| 1-2316109-4   | 14.1    | 14 |
| PART NO.      | DIM "E" | N  |



DUAL ROW HOUSING  
POLARIZED W/ LOCKING RAMP.  
1- -6 AS SHOWN

SCALE 5:1

|                                        |                                                             |                                   |                                                                   |  |
|----------------------------------------|-------------------------------------------------------------|-----------------------------------|-------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                                             | DWN 06SEP2016<br>RAKSHITH R NAYAK | TE Connectivity                                                   |  |
| DIMENSIONS:                            | TOLERANCES UNLESS OTHERWISE SPECIFIED:                      | CHK 06SEP2016<br>PRASHANTH S      |                                                                   |  |
| mm                                     | 0 PLC ±<br>1 PLC ±0.15<br>2 PLC ±0.10<br>3 PLC ±<br>4 PLC ± | APVD 06SEP2016<br>PRASHANTH S     | NAME AMPMODU 2mm RECEPTACLE, w/B HOUSING, CRIMP, DR. W/ LOCK RAMP |  |
|                                        | ±2°                                                         | PRODUCT SPEC 108-64040-1          | SIZE CAGE CODE DRAWING NO RESTRICTED TO                           |  |
| MATERIAL SEE NOTE 1                    | FINISH -                                                    | APPLICATION SPEC 114-32173        | A2 00779 C-2316109                                                |  |
| -                                      | -                                                           | WEIGHT -                          | CUSTOMER DRAWING                                                  |  |

|            |              |        |
|------------|--------------|--------|
| SCALE 10:1 | SHEET 1 OF 1 | REV A1 |
|------------|--------------|--------|