




LOC		DIST		REV		DATE		DWN		APVD	
-	-	-	-	-	-	-	-	-	-	-	-
D	REV PER ECO 13-008053					5-14-13		CT		DM	

- 1 BRASS PER ASTM B16 PLATED GOLD, .000050 MIN PER ASTM B488, TYPE 2, GRADE C OVER .000050 MIN NICKEL PER QQ-N-290.
- 2 ALUMINUM ALLOY 6061-T6 PER ASTM B221 PLATED ELECTROLESS NICKEL, .00100 MIN PER AMS-C-26074 CLASS 1.
- 3 BRASS PER ASTM B16 PLATED GOLD, .000015 MIN PER ASTM B488, TYPE 2, GRADE C OVER .000050 MIN NICKEL PER QQ-N-290.
- 4 PHOSPHOR BRONZE PER ASTM B103 PLATED GOLD, .000015 MIN PER ASTM B488, TYPE 2, GRADE C OVER .000050 MIN NICKEL PER QQ-N-290.
- 5 CONNECTOR IS MARKED WITH TE, TE CONNECTIVITY PART NUMBER AND DATE CODE, IN APPROXIMATE AREA SHOWN.
- 6 NO RADIUS ALLOWED .130 FROM HOLE $\perp$ OPPOSITE SIDE FOR MOUNTING HARDWARE CLEARANCE. (2X)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. GLATFELT CHK D. MILLER APVD D. MILLER		24FEB2011 25FEB2011 25FEB2011	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ±.01 ±.005 ± ± ±		APPLICATION SPEC	
MATERIAL SEE CALL OUT		WEIGHT -		CUSTOMER DRAWING	
AS SHOWN		DESCRIPTION		PART NUMBER	
2157447-1		TE Connectivity		ASSEMBLY, RECEPTACLE, D-SUB, QUADRAx 202, SIZE 2, RIGHT ANGLE, PCB MOUNT	
SIZE A1		CAGE CODE 00779		DRAWING NO 2157447	
SCALE 4:1		SHEET 1		OF 1	
REV D					