




THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION,ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	□	RELEASED<FC00-0149-03>	31, OCT, ' 03	MS	CS
	A	RELEASED<FC00-0027-04>	13, FEB, ' 04	MS	CS
	B	REVISED <ECR-15-010973>	23. JUL. ' 15	JM	HG



3-D VIEW
(SCALE 1/1)


NOTE;

1. GENERAL TOLERANCES : ± 0.3 , $\pm 3^\circ$.
2. 0.15 MAX. WARPAGE AND 0.2 MAX. FLASH ARE PERMISSIBLE
3. APPLICABLE CONN'R PART NO. : 936394

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



MATERIAL

SEE TABLE

0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$
ANGLES $\pm$
FINISH

DWN JM JEON

CHK JW JUNG

APVD HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
DBL HSG FOR 2.8mm SEALED 6P PLUG CONN'R

SIZE
A300779C- 936397

⑧	GRAY	PBT	0-936397-3
⑧	BLACK	PBT	0-936397-2
	YELLOW	PBT	0-936397-5
	COLOR	MATERIAL	PART NO.

SCALE 5/1 SHEET 1 OF 1 REV B