

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0857912020

Status:


Active

Overview:

Magnetic Jacks

Description:

MXMag PD Integrated Gigabit Ethernet 8 Core PoE+ 30W Class 2 Single-Port RJ45 Connector, 39.00mm Depth, 3.15mm Phy Pin Length, Right-Angle, Inverted Profile, with Shield Tabs, Non-LED, Standard Temperature, Tray



Series image - Reference only

Documents:

- 3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-85791-001-001 (PDF)
- Packaging Specification PK-85759-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Modular Jacks/Plugs
Series	85791
Component Type	PCB Jack
Depth	39.00mm
Magnetic	Yes
Overview	Magnetic Jacks
Performance Category	1000Mb
Power over Ethernet (PoE)	PoE+
Product Name	Magnetic Jack, MXMag, RJ45
UPC	887191157344

Physical

Color - Resin	Black
Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	13.87mm
Keying to Mating Part	None
Lightpipes/LEDs	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PBT
Net Weight	11.097/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Spring Tabs
Plating min - Mating	0.762µm
Port Configuration	1x1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +70°C
Termination Interface: Style	Through Hole
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.0A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	60V AC

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

85791 Series

Mates With

Plugs according to IEC 60603-7

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-85759-001-001
Product Specification	PS-85791-001-001
Sales Drawing	857910020-000

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION