



# SPECIFICATIONS






- 50 Ohms BNC R/A PCB Mount Jack
- 1.Center Contact:Bronze,Gold Plated
- 2.Body: Zinc Alloy,Nickel Plated
- 3.Housing: PBT(UL 94V-0),White
- 4.Insulator: PE-606
- 5.Mounting Post:Bronze,Tin Plated
- 6.Solder Tail: Copper Wire,Tin Plated
- 7.Washer: Steel,Nickel Plated
- 8.Nut: Brass,Nickel Plated



Recommended Mounting Hole  
Max. Panel Thickness: 5.5mm



Recommended P.C.Board Layout  
Without Mounting Posts



**4UCON** 元化興業股份有限公司  
4UCON TECHNOLOGY INC.

DRAWING No.

06542

SCALE

NONE

APPROVED BY

MEI

CHECKED BY

BECKY

DRAWING BY

HZF

REV.

BO

UNLESS OTHERWISE  
SPECIFIED  
TOLERANCES ARE


X. ±0.5

.X ±0.3

.XX ±0.2

UNIT

mm



NO. REV.

BO

NEW RELEASE

REVISIONS

BECKY

CHK

03/29/2006

DATE