

ATO® FH2 SERIES

30 A Max Stackable Block In-Line Fuse Holder



Description

Install an ATO® blade-style fuse with ease using the ATO® FH2 Stackable Block In-Line Fuse Holder. Attachable in the X- and Y-direction, this stackable fuse holder can also be used with additional ATO® FH2 fuse holders to create a fuse block for protecting multiple circuits.

The ATO® FH2 stackable fuse holder features a black, thermoplastic body with a UL 94 V-0 flammability rating for heat and flame resistance. In addition, the automotive in-line fuse holder assembly can be completed with a transparent thermoplastic cover for protection against debris.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/FH2

Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	FLAMMABILITY RATING
178.6115.0001	Thermoplastic Fuse Holder Housing - 100 Pcs.	ATO	In-Line Fuse Holder	UL 94 V-0
178.6115.0002	Thermoplastic Fuse Holder Housing - 1,000 Pcs.	ATO	In-Line Fuse Holder	UL 94 V-0
178.6116.1001	DFK Crimp Terminal - 0.5 - 1.0 mm ² - 200 Pcs.	--	--	--
178.6116.1002	DFK Crimp Terminal - 0.5 - 1.0 mm ² - 1,000 Pcs.	--	--	--
178.6116.1008	DFK Crimp Terminal - 0.5 - 1.0 mm ² - 3,000 Pcs.	--	--	--
178.6116.2501	DFK Crimp Terminal - 1.5 - 2.5 mm ² - 200 Pcs.	--	--	--
178.6116.2502	DFK Crimp Terminal - 1.5 - 2.5 mm ² - 1,000 Pcs.	--	--	--
178.6116.2508	DFK Crimp Terminal - 1.5 - 2.5 mm ² - 2,500 Pcs.	--	--	--
178.6116.6001	DFK Crimp Terminal - 4.0 - 6.0 mm ² - 200 Pcs.	--	--	--
178.6125.0001	Transparent Thermoplastic Fuse Holder Cover - 100 Pcs.	--	--	UL 94 V-0
178.6125.0002	Transparent Thermoplastic Fuse Holder Cover - 1,000 Pcs.	--	--	UL 94 V-0

Specifications

Continuous Current Rating:	30A
Fuse Type:	ATO
Flammability Rating:	UL 94 V-0 Material
Mounting Method:	In-Line Fuse Holder
Input Terminals:	Wire Crimp 6.3mm Receptacles
Output Terminals:	Wire Crimp 6.3mm Receptacles
Additional Notes:	Compatible with the FKS ATO Fuse at 80V DC

Applications

- Accessory Circuit Protection

Features and Benefits

- Compatible with ATO® blade-style fuses (sold separately)
- 30 A max continuous current rating
- Attachable in the X- and Y-direction for simple stacking or row mounting
- Heat-resistant thermoplastic fuse holder body with a UL 94 V-0 flammability rating
- Leaf spring connector system
- Wire crimp 6.3 mm receptacles
- Transparent thermoplastic cover offers protection and a clear view