






NOTE:

1. MATERIAL:
HOUSING: NYLON 6T (E630NK), UL94V-0
TERMINAL: C2700 H
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u") MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
5. MATING SIDE LENGTH: 2.50MM MIN.

6. PRODUCT NUMBERING:
200218 3 4 - XXX XX X X LF

LEAD FREE
PLATING:
1: G/F ALL OVER
4: 0.25um(10u") GOLD AT CONTACT
8: 0.76um(30u") GOLD AT CONTACT
PACKING
T: TUBE
PIN COUNT
04, 06, 08, ..., 48, 50
(EVERY EVEN PIN)

STACK HEIGHT "K"
EXAMPLE: 045=4.5MM
IN 0.5MM INCREMENT



Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.38	projection		www.fciconnect.com	
1	T10-0072	S.LIN	10'-5-31		.XX ± 0.25			title	
				angles	.XXX ± 0.15			1.27X1.27MM BTB STACK HD	
					0° ± 2°			VT, SMT	
				dr	STERLING LIN	10'-5-20		product family	
				enrg	STERLING LIN	10'-5-20		585	
				chr	STERLING LIN	10'-5-20		code	
				appd	GARY HSIEH	10'-5-20		size	
sheet	revision	A	-					size	
index	sheet	1						20021834	
								code	
								1 of 1	