

STRAIGHT PLUG, CRIMP TYPE, FOR FLEXIBLE CABLES




Fig 1





Fig 2

cable	part number	fig	capt.center cont.	assembly	finish	note
5/50 S	R185 082 027●	1	yes	M11	BBR	LMR 200 cable
10/50 S + D	R185 074 000	2	yes	M05	Silver+BBR	RG 213 & RG 393
11/50 D	R185 077 000	2	yes	M05	Silver+BBR	


STRAIGHT PLUG, CLAMP TYPE, FOR FLEXIBLE CABLES



cable	part number	capt. center cont.	assembly	finish
10 + 11/50 S + D	R185 010 000	yes	M10	Silver+BBR

- Manufactured upon request

Note : standard packaging = 20 pieces. For unit packaging, add "W" after the P/N.



STRAIGHT PLUG EZ FIT TYPE FOR CORRUGATED CABLES




Fig 1

cable	part number	fig.	dimension			capt. center cont.	assembly	finish
			A	B	C			
1/4" superflexible corrugated	R185 030 200	1	47	7.95	4.7	yes	M02	Silver+BBR
1/2" flexible corrugated	R185 031 020W	N.S.				yes		Silver
1/2" superflexible corrugated	R185 031 200	1	49	14	8.8	yes	M02	Silver+BBR
3/8" superflexible corrugated	R185 032 200	1	49	11	7.1	yes	M02	
7/8" flexible corrugated	R185 033 020W	N.S.				yes		Silver

STRAIGHT PLUG SOLDER TYPE FOR SEMI RIGID CABLES





Fig 1




Fig 2

cable	part number	fig	panel	capt. center cont.	assembly	finish	note
.141"	R185 102 400•	1	P10	yes	M13	Silver	square flange
.250"	R185 054 020•	2		yes	M12	Silver	

- Manufactured upon request

Note : standard packaging = 20 pieces. For unit packaging, add "W" after the P/N.