


REVISIONS				
ZONE	LTR	ECN	DESCRIPTION	DATE
	J	25602	REV. & REDRAWN ORIGINAL RELEASE 8-17-64 BY B.T. & J.C.B. CB 2-5-81	2-6-81
	K	38873	REVISION UPDATE	4-22-99



Tyco Dwg 1466115
Micro P/N 03202170022

NOTES: UNLESS OTHERWISE SPECIFIED

1. THIS CONNECTOR MATES WITH ALL JACKS AND RECEPTACLES IN SERIES S-50 AS LISTED IN MALCO CATALOG.
2. FOR ASSEMBLY INSTRUCTIONS SEE RF-ASMB-88. USE MALCO SPECIAL TOOL #010-0003-0000.
3. SILVER PLATE .0002 MIN. PER QQ-S-365, TYPE II, GRADE A.
4. GOLD PLATE PER MIL-G-45204 TYPE II, GRADE C, CLASS I.
5. CABLE ACCEPTANCE DIMENSIONS:
JACKET: .087 DIA. MAX.
SHIELD: .061 DIA. MAX.
DIELECTRIC: .050 DIA. MAX.
INNER CONDUCTOR: .012 DIA. NOM.

1		003-0270-0002	B.R. CAP	SILICONE RUBBER (RED) PER ZZ-R-765	5
1	3	003-0163-0001	RING, JERK	BRASS PER QQ-B-626	4
1		003-0027-0001	INSULATOR	TEFLON PER L-P-403	3
1	4	003-0359-0002	PIN	BRASS PER QQ-B-626	2
		003-1081-0000	RING, SNAP	BERYLLIUM COPPER PER QQ-C-530	
	3	003-0804-0001	NUT	BRASS PER QQ-B-626	
	3	003-1083-0001	HOUSING	BRASS PER QQ-B-626	
1		003-1084-0001	HOUSING, SUBASSY.		1
QTY.	FINISH	PART NUMBER	DESCRIPTION	MATERIAL & SPECIFICATION	ITEM NO.

PARTS LIST

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± .010 ±		CONTRACT NO.		MALCO A MICRODOT COMPANY, INC. 306 PASADENA AVE., SO. PASADENA, CALIF. 91030	PROD. CODE 931 CODE CDM
		APPROVALS	DATE		
MATERIAL NOTED		DRAWN	Gold Proum 2-6-81	PLUG	
		CHECKED	2/6/81		
		PR. ENG.	2-6-81		
FINISH NOTED		APPROVED		SIZE	B
		These drawings and specifications are the property of Microdot Inc., are issued in strict confidence and shall not be divulged, be reproduced or copied, or used as the basis for the manufacture or sale of any article without written permission of Microdot Inc.		CODE IDENT NO.	98278
NEXT ASSY	USED ON	DRAWING NO.		032-0217-0022	
APPLICATION		DO NOT SCALE DRAWING		SCALE	~
				SHEET	1 OF 1