


© 1970 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
0	NPS 70-4039	10/29/70	CER
A	REVISED C75-83	2-17-75	CER

ASSEMBLED VIEW


FOR USE WITH
RG-225/U

TABLE OF CONTENTS

ITEM	QTY	DESCRIPTION	PART NO.
1	1	RTANGLE PLUG ASSY	225518-3
2	1	CONTACT	225471-7
3	1	FERRULE	331987
4	1	SEAL	332022

CRIMP WITH TOOL 220015-1

SEE I.S. 2299-5

RECOMMENDED
STRIP LENGTH

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES
TOLERANCES ON:
DECIMALS ± .005
ANGLES ± .5°

MATERIAL

S

CONTRACT NO.

DR.

APPD

REL

DESIGN APPD

OTHER APPD

AMP

AMP INCORPORATED
HARRISSBURG, PENNSYLVANIA

NAME

CONNECTOR, COAXIAL, R.F.
SERIES TNC- DUAL CRIMP
RIGHT ANGLE PLUG-WEATHERPROOF

SIZE

A

CODE IDENT NO.

00779

NUMBER

225554-7

SCALE

SHEET

1 OF 1